

Galden<sup>®</sup>



**SOLVAY**

asking more from chemistry<sup>®</sup>

# Galden<sup>®</sup> PFPE Testing

Electronic Fluids

**SPECIALTY  
POLYMERS**

# Galden® PFPE Testing

## Electronic Fluids

Galden® PFPE electronic fluids is a line of dielectric fluids with boiling points ranging from 55°C to 270°C. Their excellent dielectric properties, high chemical and thermal

stability combined with their capacity to operate at very low as well as elevated temperatures make them ideal for electronic quality testing.

### Features

High boiling point with low pour point and low viscosity  
 Low evaporation rate  
 Good heat transfer performance

High dielectric strength  
 Excellent electrical resistivity (a billion times higher than DI-Water)  
 No change in dielectric properties with use

Excellent thermal and chemical stability  
 Good compatibility with materials

No flash or fire points  
 No auto ignition point  
 No explosion hazards

### Benefits

Wide choice of grades to optimize performance  
 Low consumption  
 Low environmental load  
 Better temperature control

No damage to sensitive electronics when immersed in the liquid  
 No risk of short circuiting  
 Better process control

No corrosion or reaction with materials of construction  
 No formation of decomposition residues

Enhanced safety  
 Safe to use at high temperature

Fluids non-reactivity, excellent dielectric properties, non-toxicity, non flammability and non-solvent features make Galden® PFPE electronic fluids suitable for electronic reliability testing including thermal shock and hermetic seal testing.

## Galden® PFPE Thermal Shock Testing

### Thermal Shock: The Test

Thermal shock testing is performed to check the resistance of electronic devices to extreme changes of temperature. The test is carried out by alternately dipping the devices in liquids maintained at two different temperatures.

For military applications thermal shock test has to be performed as specified in MIL STD 883 method 1011 or MIL STD 202 method 107.

## Dual Fluid or Single Fluid?

### Dual Fluid System

Traditionally two different fluids can be used in the hot and cold bath, but this practice presents the following disadvantages: high fluid loss from cold bath, cross contamination between cold and hot baths, equipment downtime and dual fluid inventory.

### Single Fluid System

Galden® PFPE fluids with their single fluid system is an advantageous alternative to the dual fluid solution.

Galden® D02TS and D03 are the single fluids which can successfully replace the need for a dual fluid system.

Galden® D02TS is the proposal for all the military applications; it meets the MIL STD 883 and MIL STD 202 while for all non-military applications Galden® D03 can be used.

A single fluid for both baths allows for a dramatic decrease in operating costs by:

- Decreasing fluid consumption
- Reducing equipment downtime
- Eliminating cross contamination
- Reducing inventory to a single product

**Galden® PFPE fluids for thermal shock testing** conforming to MIL STD 883

	Test Condition				
	B	C	D	E	F
Hot Step [°C]	125	150	200	150	200
Cold Step [°C]	-55	-65	-65	-195	-195
Hot Bath Fluid	D02 D02TS	D02 D02TS	D05	D02 D02TS	D05
Cold Bath Fluid	DET D02TS	DET D02TS	DET	Liquid N <sub>2</sub>	Liquid N <sub>2</sub>

## Galden® PFPE Hermetic Seal Testing

### Hermetic Seal: The Test

Electronic devices must be completely sealed to avoid penetration by moisture and potential damage of the electrical response of the silicon chip.

To guarantee the hermeticity of devices, a leak test procedure has been defined and ruled by MIL STD 883, MIL STD 750 and MIL STD 202.

Galden® PFPE fluids being extremely inert and residue free are ideal and widely used as detector and indicator fluids in leak test procedures.

### Galden® DET

Detector fluid specifically designed for high reliability measures.

Galden® DET, Type I and III detector fluid, offers higher reliability with respect to traditionally used fluids.

Galden® DET, thanks to its perfect balance between low and high boilers components, can easily detect large and small leaks:

- High boilers enter through large leaks and remain liquid until the test is performed
- Low boilers can easily penetrate into small leaks

### Thermal shock testing

Typical Properties	Units	Single Fluids		Dual Fluids	
		D02TS	D03	D02	D05
Boiling point	°C	165	203	175	230
Pour point	°C	-97	-85	-97	-77
Density at 25 °C	g/cm <sup>3</sup>	1.77	1.79	1.77	1.82
Density at -54 °C	g/cm <sup>3</sup>	1.95	1.96	1.95	1.98
Kinematic viscosity at 25 °C	cSt	1.7	2.4	1.8	4.4
Kinematic viscosity at -54 °C	cSt	45	160	-	-
Specific heat at 25 °C	J/Kg·°C	973	973	973	973
Thermal conductivity at 25 °C	W/m·°C	0.07	0.07	0.07	0.07
Coefficient of expansion	cm <sup>3</sup> /cm <sup>3</sup> ·°C	0.0011	0.0011	0.0011	0.0011
Surface tension	dyne/cm	16	16	16	17
Dielectric strength	kV (2.54 mm gap)	40	40	40	40
Dielectric constant	-	2.1	2.1	2.1	2.1
Volume resistivity	Ohm·cm	5·10 <sup>15</sup>	5·10 <sup>15</sup>	5·10 <sup>15</sup>	5·10 <sup>15</sup>
Average molecular weight	amu	750	870	760	1,020

*Typical properties (Not for specification purpose)*

## Galden® D02 and D03

Low consumption indicator fluids.

Galden® D02 and D03 can be advantageously used as Indicator fluids respectively in military and non-military applications.

- Higher boiling point
- Lower vapor pressure at test temperature

### Will Result in...

- Reduced evaporative loss
- Lower consumption compared to other commercially available indicator fluids

### Galden® PFPE fluids for gross leak test

conforming to MIL STD

Fluid Type	Type I Detector	Type II Indicator	Type III Detector
Test Condition	C1, C3	C1	E
Galden® Fluids	DET	D02	DET

## Hermetic seal testing

Typical Properties	Units	Detector Fluids		Indicator Fluids	
		DET	D02	D03	
Boiling point	°C	81	175	203	
Pour point	°C	-110	-97	-85	
Density at 25 °C	g/cm <sup>3</sup>	1.70	1.77	1.79	
Density at 125 °C	g/cm <sup>3</sup>	-	1.54	1.58	
Kinematic viscosity at 25 °C	cSt	0.60	1.80	2.40	
Kinematic viscosity at 125 °C	cSt	-	0.46	0.55	
Specific heat at 25 °C	J/Kg·°C	973	973	973	
Thermal conductivity at 25 °C	W/m·°C	0.07	0.07	0.07	
Coefficient of expansion	cm <sup>3</sup> /cm <sup>3</sup> ·°C	0.0011	0.0011	0.0011	
Surface tension	dyne/cm	16	16	16	
Dielectric strength	kV (2.54 mm gap)	40	40	40	
Dielectric constant		2.1	2.1	2.1	
Volume resistivity	Ohm·cm	5·10 <sup>15</sup>	5·10 <sup>15</sup>	5·10 <sup>15</sup>	
Average molecular weight	amu	430	760	870	

Typical properties (Not for specification purpose)

[www.solvay.com](http://www.solvay.com)

[SpecialtyPolymers.EMEA@solvay.com](mailto:SpecialtyPolymers.EMEA@solvay.com) | Europe, Middle East and Africa

[SpecialtyPolymers.Americas@solvay.com](mailto:SpecialtyPolymers.Americas@solvay.com) | Americas

[SpecialtyPolymers.Asia@solvay.com](mailto:SpecialtyPolymers.Asia@solvay.com) | Asia Pacific



**SOLVAY**

asking more from chemistry®

Safety Data Sheets (SDS) are available by emailing us or contacting your sales representative. Always consult the appropriate SDS before using any of our products. Neither Solvay Specialty Polymers nor any of its affiliates makes any warranty, express or implied, including merchantability or fitness for use, or accepts any liability in connection with this product, related information or its use. Some applications of which Solvay's products may be proposed to be used are regulated or restricted by applicable laws and regulations or by national or international standards and in some cases by Solvay's recommendation, including applications of food/feed, water treatment, medical, pharmaceuticals, and personal care. Only products designated as part of the Solviva® family of biomaterials may be considered as candidates for use in implantable medical devices. The user alone must finally determine suitability of any information or products for any contemplated use in compliance with applicable law, the manner of use and whether any patents are infringed. The information and the products are for use by technically skilled persons at their own discretion and risk and does not relate to the use of this product in combination with any other substance or any other process. This is not a license under any patent or other proprietary right. All trademarks and registered trademarks are property of the companies that comprise Solvay Group or their respective owners.

© 2014 Solvay Specialty Polymers. All rights reserved. R 10/2014 | Version 2.1 Brochure design by ahlersheinel.com